

# Prisma Daps

**EXTERNAL LOUDSPEAKER**

**ES-400**



*Sound recommended by  
The Swedish Association of the  
Visually Impaired*

 **PRISMATIBRO**

# Prisma Daps

## PRISMA DAPS ES-400 EXTERNAL LOUDSPEAKER

### External Loudspeaker

Prisma Daps ES-400 can be used with the acoustic pedestrian signals as a external loudspeaker. Especially effective in noisy intersections with need of a strong sound focused directly to the pedestrians that will cross the intersection.

### Noise Control by Prisma Daps

Noise control is regulated by the Prisma Daps 2000 which the external loudspeaker ES-400 is connected to.

### Amplifies

Prisma Daps ES-400 amplifies the locator sound during green phase. The locator sound is help for pedestians to locate and get the status of the intersection.

### Mounting

To be mounted on the pole, about 2.5 meter above the ground level, facing the opposite side of the crosswalk/street.

### Aluminum

Prisma Daps ES-400 is a strong and reliable loudspeaker protected by the housing of anodized aluminum profile.

### Cabling

Included: 3 meters Ölflex 2x0,75mm<sup>2</sup>

Required: Prisma Daps connected with 10- or 13-wire cabling.

### Connection


Directly connected to all

- Prisma Daps 2000•L-series
- Prisma Daps 2000•M-series

### Sound & Volume

Use the Android App Prisma Daps to

- Select sound
- Adjust the sound level
- Activate the noise control
- Record your own sound/messages



## TECHNICAL INFORMATION

Frequency range	180-7000 Hz
Weight	0.8 kg
Height, width, depth	95 x 110 x 60 mm



ADDRESS Jarnvagsgatan 19, SE-543 50Tibro  
SWITCHBOARD +46 504 400 40  
WEB [prismatibro.se](http://prismatibro.se)  
E-MAIL [contact@prismatibro.se](mailto:contact@prismatibro.se)